

Архангельск (8182)63-90-72
Астана (7172)727-132
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16

Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13

Сургут (3462)77-98-35
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93

<http://cannon.nt-rt.ru> || cnn@nt-rt.ru

Денситометры CANNON

Техническое описание

D155 Density/Specific Gravity Meter

The automated CANNON D155 offers a low-cost, affordable alternative to manual hydrometer methods for measuring density and specific gravity with easy, one button operation. Built-in thermal control provides quick, precise measurement with 4 decimal resolution.



Dimensions (W × D × H)	25.1 cm × 40.8 cm × 16.5 cm (10.0 in × 16.0 in × 6.5 in)	
Weight	11.6 kg (25.6 lb)	
Test range and precision	Density	0 g/cm ³ to 2 g/cm ³ ± 0.001 g/cm ³
Resolution	Density	0.0001 g/cm ³
	Temperature	0.05 °C
	Specific gravity	0.0001 step
	Temperature compensated parameters	0.0001 step
	API degree	0.1 step
Repeatability	Density	SD 0.0005 g/cm ³
Temperature range and accuracy	15 °C to 25 °C (0.1 °C step)	
Minimum sample volume	Manual (syringe): 1 mL With peristaltic pump: 8 mL	
Operating conditions	5 °C to 35 °C, <85% relative humidity (non-condensing)	
Electrical specifications	100 VAC to 240 VAC, 50/60 Hz; ~30 watts power consumption	
Data output	RS-232C and USB	

Densi-H Handheld Density/Specific Gravity Meter

For On-site Measurement of Density, Specific Gravity and API Degrees ASTM D7777

The handheld Densi-H is CANNON's most affordable instrument for measuring density and specific gravity. Lightweight and portable, Densi-H offers easy, one button operation and reports results in seconds. Densi-H operates on the oscillating tube principle.



Dimensions (W × D × H)		7.6 cm × 12.7 cm × 25.4 cm (3 in × 5 in × 10 in)
Weight		0.36 kg (0.8 lb)
Test range & accuracy	Density	0 g/cm ³ to 2 g/cm ³ ± 0.001 g/cm ³
Resolution	Density	0.0001 g/cm ³
	Temperature	0.01 °C
Temperature range and accuracy		5 °C to 35 °C ± 0.1 °C
Operating conditions		-20 °C to 70 °C, <85% relative humidity (non-condensing)
Electrical specifications		Battery powered (2 AAA batteries)
Data output		Infrared / RS-232

Архангельск (8182)63-90-72
Астана (7172)727-132
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16

Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13

Сургут (3462)77-98-35
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93